

Duomax 1030 (5° tilt angle)

P/N: 543-32205-00



Containers are safely fixed on the anti-slip rubber mat even at high speeds. The speed is variably adjustable between 2 and 50 rpm. The shaker can be operated in continuous operation or with a timer (max. 120 minutes).

A tilt angle of 5° is recommended for applications for which a gentle movement amplitude is suitable.

Additionally, the Duomax 1030 can be integrated into the modular incubator model.

Duomax 1030 (5° tilt angle) - Technical Data

Overheat protection	self-resetting
Permissible ambient conditions	5 - 31 °C at 80 % rel. humidity 32 - 40 °C decreasing linearly up to max. 50 % rel. humidity
Weight	8 kg
Protection class IEC 60529	IP 20
Timer	yes (max. 120 min)
Rotation speed range	2 - 50 rpm
Power input	115 W
Dimensions (w/d/h)	320 x 375 x 185 mm
Max. Load	5 kg
Operating Mode	timer or continuous
Rotation speed setting	electronic control
Orbit / Stroke	-
Platform size	290 x 258 mm
Accessories included	non-skid rubber mat
Angle	5°
Motion	rocking